

**Rittal – The System.**

Faster – better – everywhere.



# SV 3454.500 Conductor connection clamp

State: 2026.4.21 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3454.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

## Features

|   |  |
|---|--|
| Model No.                                       | SV 3454.500  |
| Product description                             | For connecting round conductors and laminated copper bars.   |
| Material  | Sheet steel  |
| Surface finish                                  | Zinc-plated, passivated  |
| Clamping area for laminated copper bars (W x H) | 22.5 x 20 mm   |
| Note  | Wire end ferrules should be used with fine wire conductors   |
| Connection of round conductors                  | 70 - 185 mm <sup>2</sup>   |
| For bar thickness                               | 5 mm   |
| Packs of  | 15 pc(s).  |
| Net weight                                      | 1.95 kg  |
| Gross weight                                    | 1.982 kg   |
| PCF per pack (cradle-to-gate)                   | 7.6 kg CO2 eq (Cat B)  |
| Note on PCF category                            | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number                           | 85369010   |
| ETIM 9  | EC000001   |
| ETIM 8  | EC000001   |
| ECLASS 8.0                                      | 27141146   |
| Product description                             | SV Conductor connection clamp, 70-185 mm <sup>2</sup> , clamping area WH: 22,5x20 mm, for bar thickness 5 mm   |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---

## Tender text

SV conductor connection clamps  
for E-CU busbars and Rittal PLS.  
for bar thickness: 5 mm  
Connection of round conductors 70 - 185 mm<sup>2</sup>  
Wire end ferrules should be used with  
fine wire conductors.  
Clamping area: for laminated  
copper bars 22.5 x 20 mm  
Tightening torque  
Conductor connection clamp: 12 - 15 Nm  
Material: sheet steel, zinc plated, passivated