Rittal – The System.

Faster – better – everywhere.





SK 3310.740

Modular climate control concept -Cooling module "Blue e"

State: 2025.11.27 (Source: rittal.com/lt-en)



SK 3310.740 - Modular climate control concept - Cooling module "Blue e" Total cooling output 1.50 - 2.50 kW

Cooling module for climate control doors. Cooling output from 1500 to 2500 W.





Features

| Model No. | SK 3310.740 |
|---|---|
| Product description | All cooling modules may be individually combined with any climate control door. The cooling modules are equipped with energy-efficient Blue e technology, with integral e-Comfort controller and electric condensate evaporation as standard. |
| Benefits | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Condenser with hydrophobic RiNano coating Cooling module prepared for installation in climate control door Integral electric condensate evaporation Fully wired ready for connection (plug-in terminal strip) |
| Rated current max. | At 50 Hz: 3.5 A At 60 Hz: 3.7 A |
| Start-up current max. | At 50 Hz: 13 A At 60 Hz: 14 A |
| Power consumption Pel 50/60 Hz L35 L35 | 1.41 kW/1.82 kW |

© Rittal 2025

Features

| Power consumption Pel 50/60 Hz L35 L50 | 1.54 kW/2.08 kW |
|---|---|
| Temperature control | e-Comfort controller (factory setting +35 °C) |
| At 60 Hz | 3.7 A |
| Note | A base/plinth with a height of 100 or 200 mm is required for efficient operation |
| Air throughput (unimpeded air flow) | External circuit: 1,100 m³/h Internal circuit: 1,100 m³/h |
| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 1 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.63 t |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 1.91 Refrigeration factor L35 L35 (EER) 60 Hz: 1.51 |
| Operating temperature range | 10 °C54 °C |
| Permissible operating pressure (p. max.) | 30 bar |
| Setting range | 20 °C53 °C |
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 2.7 kW Cooling output L35 L35/60 Hz: 2.75 kW Cooling output L35 L50/50 Hz: 1.76 kW Cooling output L35 L50/60 Hz: 1.9 kW |
| Rated operating voltage | 400 V, 3~, 50 Hz 460 V, 3~, 60 Hz |
| Packs of | 1 pc(s). |
| Net weight | 73 |
| Gross weight | 77 |
| Customs tariff number | 84158200 |
| EAN | 4028177559820 |
| ETIM 9 | EC002510 |
| ETIM 8 | EC002510 |
| | |

© Rittal 2025 3

Features

Approvals

| Approvals | UL + C-UL (listed) UR + C-UR (recognized) |
|--------------|---|
| Certificates | EAC |
| Explanations | Declaration of conformity Declaration of conformity - F-gas regulation |

© Rittal 2025