Rittal – The System.

Faster – better – everywhere.





SV 3563.000 Plate clamp

State: 2025.12.14 (Source: rittal.com/lt-en)



SV 3563.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

Model No.	SV 3563.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	54 x 10 mm
To fit busbars	60 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Net weight	1.35
Gross weight	1.569
PCF per pack (cradle-to-gate)	6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177044418
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

© Rittal 2025

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

Plate clamps

for E-Cu busbars with 3 - 10 mm thickness.

For bar width: up to 60 mm

Clamping area for laminated copper bars:

54 x 10 mm

Tightening torque: 6 - 8 Nm

Material: Sheet steel, zinc-plated, passivated

© Rittal 2025