
Rittal – The System.

Faster – better – everywhere.



SV 3585.020

CUPONAL busbars


State: 2026.10.30 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3585.020 - CUPONAL busbars

Copper-coated aluminium busbar





Features

Model No.	SV 3585.020
Product description	Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050.
Material	Aluminium Copper
Rated current max.	363 A
Note	The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length
Standards	DIN EN 13 601
Cross-section	20 mm x 10 mm
Dimensions	Length: 2,400 mm
Packs of	3 pc(s).
Net weight	6.3 kg
Gross weight	6.5 kg
Copper weight (kg per piece)	0.7
Customs tariff number	76042990

© Rittal 2026

Features

ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303
Product description	SV Busbar CUPONAL, WH: 20x10 mm, L: 2400 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK