


Rittal – The System.

Faster – better – everywhere.



AS 4050.010 Enclosure machining

State: 2024.5.17 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.010 - Enclosure machining for Perforex BC 1001 HS

Machine equipped with door and pneumatic clamping device. The corresponding support surface enables the machining of cubes up to a maximum depth of 1400 mm. For additional machining of enclosures that cannot be dismantled on Perforex machining centres BC.

Features

| | |
|-------------------------------------|---|
| Model No. | AS 4050.010 |
| Design | Machining surface with door Pneumatic clamping device Additional support surface Mechanical depth adjuster |
| Product description | Machine equipped with door and pneumatic clamping device. The corresponding support surface enables the machining of cubes up to a maximum depth of 1400 mm. For additional machining of undismantable enclosures on Perforex machining centres BC. |
| Benefits | Depth-variable Use of the existing machine surface for the additional machining of cubes |
| Note | Not suitable for retrofitting |
| To fit Model No. | 4050.101 |
| Dimensions of clampable cubic parts | Width: 1,200 mm Height: 1,400 mm Depth: 1,400 mm |
| Max. machinable area | Width: 750 mm Height: 1,400 mm |
| Packs of | 1 pc(s). |
| Customs tariff number | 84669360 |
| EAN | 4028177804159 |
| ETIM 7.0 | EC003456 |
| ECLASS 8.0 | 36609190 |