

**Rittal – The System.**

Faster – better – everywhere.



**SK 3329.518**

**TopTherm wall-mounted cooling  
unit Blue e, UL Type 3R/4**

State: 2026.4.23 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3329.518 - TopTherm wall-mounted cooling unit

## Blue e, UL Type 3R/4 0.5 - 2.5 kW

Energy-efficient Blue e wall-mounted cooling units in output categories 500 W to 2,500 W with integral e-Comfort controller and electric condensate evaporation (from 1000 W) as standard, protection category UL Type 3R/4, 12.



## Features

Model No.	SK 3329.518
Design	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category UL Type 3R/4, 12.
Benefits	Suitable for outdoor siting Blue e technology May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation

# Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.55 kW Cooling output L35 L35/60 Hz: 2.6 kW Cooling output L35 L50/50 Hz: 1.8 kW Cooling output L35 L50/60 Hz: 1.8 kW
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 17 A At 60 Hz: 22 A
Start-up current max.	At 50 Hz: 44 A At 60 Hz: 42 A
Air throughput (unimpeded air flow)	External circuit: 710 m <sup>3</sup> /h Internal circuit: 640 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.11 Refrigeration factor L35 L35 (EER) 60 Hz: 1.7
Design	wall-mounted
Dimensions	Width: 405 mm Height: 1,650 mm Depth: 388 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 56
Protection category NEMA	UL Type 3R UL Type 4 UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.1 kg Global Warming Potential (GWP): 631 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.69 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	-20 °C...50 °C
Operating temperature	Compressor cooling mode from +10 °C ambient temperature. Only the internal fan is active in the temperature range -20 °C to +10 °C.
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...50 °C

# Features

---

Power consumption Pel	Power consumption L35 L35/50 Hz: 1.21 kW Power consumption L35 L35/60 Hz: 1.53 kW Power consumption L35 L50/50 Hz: 1.41 kW Power consumption L35 L50/60 Hz: 1.8 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Transformer circuit-breaker: 18...25 A
Packs of	1 pc(s).
Net weight	95 kg
Gross weight	108 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, UL Type 3R/4, 2.51 kW, 115 V, 1~, 50/60 Hz, sheet steel, WxHxD: 405 x 1650 x 388 mm

---

# Approvals

---

Approvals	UL + C-UL (listed) UL + C-UL - FTFA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK

---