

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.125**

**Splitter hole punch, round**

State: 2026.4.14 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.125 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

## Features

Model No.	AS 4055.125
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Machinable material	Stainless steel
Maximum machinable material thickness, stainless steel	2 mm
Ø punch	25.4 mm
For threads	M25
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.665
Tension screw (Ø x L)	11.1 x 60 mm
Hydraulic tension screw Ø	11.1 mm 19 cm
Packs of	1 pc(s).
Net weight	0.121 kg
Gross weight	0.142 kg
Customs tariff number	82073010
ETIM 9	EC000156

# Features

---

ETIM 8	EC000156
ECLASS 8.0	21049047
Product description	Splitter hole punch, round for stainless steel, round, with triple splitting

---