


Rittal – The System.

Faster – better – everywhere.



AS 4055.180

Splitter hole punch set, metric

State: 2025.8.21 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.180 - Splitter hole punch set, metric for stainless steel, round, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.180 |
| Design | With triple splitting |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | 5 female dies 5 male dies Plastic case |
| Machinable material | Stainless steel |
| Maximum machinable material thickness, stainless steel | 2 mm 2 mm 2 mm 2.5 mm 2.5 mm |
| Ø punch | 16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm |
| For threads | M16 M20 M25 M32 M40 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |

Features

| | |
|--|---------------|
| Suitable for hydraulic bolt order number | 4055.665 |
| | 4055.665 |
| | 4055.665 |
| | 4055.663 |
| | 4055.663 |
| Packs of | 1 pc(s). |
| Net weight | 0.849 |
| Gross weight | 1.098 |
| Customs tariff number | 82034000 |
| EAN | 4028177808171 |
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21049047 |