### Rittal – The System.

Faster – better – everywhere.







# AS 4055.240 Hole punch, round

State: 2025.11.10 (Source: rittal.com/lt-en)



## AS 4055.240 - Hole punch, round for sheet steel

For punching round cut-outs

#### **Features**

Model No.	AS 4055.240
Design	With 3 cutting points
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	40.5 mm
For threads	M40
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.522
Gross weight	0.554
Customs tariff number	82073010
EAN	4028177808300
ETIM 9	EC000156
ETIM 8	EC000156

© Rittal 2025

#### Features

ECLASS 8.0

21049047

© Rittal 2025 3