
Rittal – The System.

Faster – better – everywhere.



SV 3515.000

PLS busbar connectors


State: 2026.10.31 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3515.000 - PLS busbar connectors

For connecting PLS special busbars, no drilling required.



Features

Model No.	SV 3515.000
Product description	For connecting the PLS special busbars, no drilling required.
Material	E-Cu
Surface finish	Nickel-plated
Rated current (max.)	1,368 A
To fit busbars	PLS 1600
To fit Model No.	9342.000 9342.004 9342.050
Connection type	Baying connection from enclosure to enclosure
Dimensions	Length: 150 mm
Packs of	3 pc(s).
Net weight	3.81 kg
Gross weight	4.015 kg
Copper weight (kg per piece)	1.27
Customs tariff number	85369010
ETIM 9	EC000713
ETIM 8	EC000713

© Rittal 2026

Features

ECLASS 8.0	27400606
Product description	SV Busbar connector, PLS 1600, bayed connection

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

PLS 1600 busbar connector
System
Rittal RiLine60
Description
PLS 1600 busbar connector for connecting the
PLS 1600 special busbar
Design
Baying connection from enclosure to enclosure
Material properties
E-Cu, nickel-plated
Screw M10
Tightening torque
20 Nm
Note
The use of cross members 9340240/230 is compulsory
for UL 508A applications.