

Rittal – The System.

Faster – better – everywhere.



AS 4054.023 Crimping pliers

State: 2026.4.17 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.023 - Crimping pliers for ring terminals

For use with non-insulated ring terminals



Features

| | |
|-----------------------|---|
| Model No. | AS 4054.023 |
| Design | Straight |
| Product description | For use with non-insulated ring terminals. |
| Benefits | Releasable ratchet Optimised lever transmission means that only minimal actuator forces are required, even with large cross-sections |
| Material | High-quality special tool steel |
| Surface finish | Matt, plated |
| Colour | Handle: Anthracite and Rittal Power Pink |
| Compression | Double-indent crimp |
| Dimensions | Height: 68 mm Length: 256 mm |
| AWG | 12 - 8 |
| For cross-section | 4 - 10 mm ² |
| Packs of | 1 pc(s). |
| Net weight | 0.63 kg |
| Gross weight | 0.668 kg |
| Customs tariff number | 82032000 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000168 |
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |
| Product description | Crimping plier 4 - 10 mm ² , d-indent |
