Rittal – The System.

Faster – better – everywhere.



TS 4163.000
Threaded blocks

State: 2026.10.30 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 4163.000 - Threaded blocks

Used on enclosures and rails with rectangular system punching 12.5 x 10.5 mm with snap-off insertion aid, die-cast zinc.



Features

Model No.	TS 4163.000
Product description	With snap-off insertion aid, die-cast zinc.
Installation options	On the horizontal and vertical VX enclosure section On the vertical TS, VX SE enclosure section via adaptor rails for VX compatibility On the horizontal TS enclosure section On the horizontal VX SE enclosure section, bottom On the horizontal VX SE enclosure section, top in the depth On punched rails 23 x 23 mm On punched section without mounting flange, 23 x 73 mm On punched section without mounting flange, 45 x 88 mm On punched sections with mounting flanges, 23 x 64 mm On punched sections with mounting flanges, 23 x 73 mm On punched sections with mounting flanges, 23 x 89 mm, stainless steel On enclosures and rails with rectangular system punching 12.5 x 10.5 mm.
Dimensions	Thread: M8
To fit enclosure type	VX TS VX SE
Thread	M8

© Rittal 2026

Features

Packs of	50 pc(s).
Net weight	0.4 kg
Gross weight	0.461 kg
Customs tariff number	73181692
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815
Product description	TS Threaded block, for thread M8

© Rittal 2026