Rittal – The System.

Faster – better – everywhere.



VX 5301.331

Gland plate modules, vented

State: 2026.11.4 (Source: www.rittal.com/lt-en)

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 5301.331 - Gland plate modules, vented for VX IT

For closing the base

Features

Model No.	VX 5301.331
Product description	For closing the base
Benefits	Large perforated section to support passive climate control of the enclosure Filter mat slides in from above for easy replacement
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Gland plate modules, vented Filter mat Assembly parts
Assembly instruction	Several gland module plates must be combined to seal the base completely in the VX IT The gland plate module may be combined in exchange with other base modules with a depth of 237.5 mm.
Dimensions	Depth: 237.5 mm
To fit	Enclosure type: VX IT Width: = 800 mm
Packs of	1 pc(s).
Net weight	2 kg
Gross weight	2.38 kg
PCF per pack (cradle-to-gate)	9.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2026

Features

Product description	VX IT gland plate module, ventilated, for width 800 mm, W x D 800 x 237.5 mm, sheet steel