


# Rittal – The System.

Faster – better – everywhere.



## DK 5526.141

## Network/server enclosure TS IT

State: 2025.9.12 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5526.141 - Network/server enclosure TS IT with glazed door, with 482.6 mm (19") mounting frame

TS IT, sealed, for direct climate control tailored to the specific enclosure. 482.6 mm (19") interior installation with 482.6 mm (19") mounting frame for a load capacity of up to 1,500 kg, available in a range of size variants.

## Features

|                     |   |
|---------------------|---|
| Model No.           | DK 5526.141   |
| Product description | TS IT, glazed door, solid rear door, 482.6 mm (19") mounting frame  |
| Material            | Sheet steel<br>Aluminium<br>Glazed door: Single-pane safety glass, 3 mm   |
| Surface finish      | Enclosure frame: Dipcoat-primed<br>Interior installation: Dipcoat-primed<br>Doors and roof: Dipcoat-primed, powder-coated   |
| General colour      | RAL 7035  |
| Colour              | Enclosure frame and panels: RAL 7035<br>Interior installation: RAL 9005   |
| Supply includes     | TS 8 enclosure frame with doors and roof plate<br>Glazed aluminium door at the front, 180° hinges<br>Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E<br>Two 482.6 mm (19") mounting frames, front and rear, depth-variable<br>Spacers, height 50 mm, to raise a cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose). Not required for variants without a cut-out.<br>Connection accessories for potential equalisation with earthing point (supplied loose)<br>12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose)<br>50 multi-tooth screws, conductive (supplied loose)<br>IPPC pallet<br>Roof plate, multi-piece, removable, for horizontal cable entry at the rear and with covered cut-out for fan mounting plate<br>Sheet steel door at the rear, 180° hinges |

## Features

|   |   |
|---|---|
| Dimensions  | Width: 600 mm<br>Height: 1,200 mm<br>Depth: 600 mm  |
| Units   | 24 U  |
| Units   | 24 U  |
| Free mounting space to the 482.6 mm (19") level, front/rear | 84 mm / 168 mm  |
| Distance between levels as delivered                        | 345 mm  |
| Design doors  | solid   |
| 482.6 mm (19") level(s) version                             | Mounting frame, 482.6 mm (19")  |
| Load capacity   | 15,000 N  |
| Note  | Depending on how and where it is sited, the door opening angle may vary for selected applications |
| Basic material  | Aluminium   |
| Packs of  | 1 pc(s).  |
| Net weight  | 67.1  |
| Gross weight  | 70.6  |
| EAN   | 4028177705838   |
| E-Number Sweden   | E7239870  |
| ETIM 9  | EC002499  |
| ECLASS 8.0  | 27180207  |

## Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Certificates | Surface finish            |
| Explanations | Declaration of conformity |

# Tender text

TS IT 5526.141

TS IT network server rack for rack climate control

IT rack for climate control. Installation height 24 U, glazed front door, solid sheet steel door at the rear, multi-piece roof plate for cable entry at the rear, horizontal, open base frame, without side panels. Pre-configured with two 482.6 mm (19") mounting frames, front and rear.

482.6 mm (19") assembly parts and complete earthing kit supplied loose. Side panels, one-piece screw-fastened, base mount, gland plates available from the accessories range.

Pre-configured IT rack consisting of torsionally stiff, welded symmetrical frame of rolled 16-fold vertical sections connected with two horizontal frames of rolled 9-fold sections with integral channel for accommodating the adjacent panel seal and protecting it against possible effect of aggressive media.

All frame sections, with integral system punchings on a 25 mm DIN pitch pattern, allow convenient interior installation by simple fitting and securing of equipment. All sections have chamfered edges. The vertical frame sections have two depth/width - recessed mounting levels each, which can individually be used for flexible attachment of the installation components.

Enclosures are bayable on all sides: on the left, right, front and rear at the top or round corners.

Glazed front door made from 3 mm single-pane safety glass (ESG), in a frame of aluminium sections, with foamed-in seal, two-point locking rod, comfort handle for semi-cylinder (30/10) mm, with security lock 3524. Two hinges, with captive hinge pins, door opening angle with stand-alone sitting 180°, door hinge may be swapped to opposite side without dismantling locking rods.

Sheet steel rear door with foamed-in seal, two-point locking rod, comfort handle for semi-cylinder (30/10) mm, with security lock 3524 E. Two hinges, with captive hinge pins, door opening angle with stand-alone sitting on both sides 180°.

Multi-piece roof plate for rear cable entry via brush strips across the entire enclosure width. Roof plate for retrofitting, removable despite already made cable routing. Cut-out for accommodating a fan module already integrated and closed by a cover. For supporting passive ventilation it is possible to raise the cover by means of spacers.

Side panels are not included with the supply. One-piece, screw-fastened

side panels are available from the accessories range.

Open base frame, gland plates, function units may be retrofitted from the range of accessories. All screw-fastened panels have automatic potential equalisation and are prepared for attachment of earthing straps.

Pre-configured with two 482.6 mm (19") mounting frames, front and rear.

The static total load capacity of both mounting levels is 15,000 N.

Mounting frame consisting of universal mounting angles for server, network and electronic applications welded to a torsionally stiff all-round frame using horizontal connection sections. Depth-variable, screw-fastened via the slot attachment with the horizontal frame of the enclosure rack.

Mounting frames, front and rear, including additional pitch pattern of holes (U centre attachment) according to standard EIA 310 E. All height units are labelled and numbered in the opposite direction on the front and rear mounting level. U labelling of mounting levels can be read from the outside for easy assembly.

Mounting angles of front mounting frame, prepared for toolless accommodation of cable routing aids and organisation of structured cabling in maximum packaging density or for equipment with a sensor strip for automatic identification of the installed components by means of Radio Frequency Identification (RFID).

Mounting angles of rear mounting frame, prepared for accommodation of a Power Distribution Unit (PDU) in 1 U form factor on both sides for enclosure electrical power distribution, without waste of installation volume thanks to space-saving side mounting between mounting level and side panel in the Zero-U space.

Material: Sheet steel, aluminium

Surface finish: Panels, doors, interior installation, RAL 7035/9005

Approvals: UL, cUL

Dimensions (WxHxD): 600x1200x600 mm

Model No.: TS IT 5526.141

Manufacturer: Rittal GmbH & Co. KG