

# Rittal – The System.

Faster – better – everywhere.



## VX\_IT 5302.167 Cross-member

State: 2025.8.15 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX\_IT 5302.167 - Cross-member for VX IT 482.6 mm (19") mounting angles

For depth- and width-variable mounting of 482.6 mm (19") mounting angles, standard, in 800 mm wide VX IT network/server enclosures.

## Features

Model No.	VX IT 5302.167
Design	for VX IT 482.6 mm (19") mounting angles, standard
Product description	For width-variable mounting of standard 482.6 mm (19") mounting angles in 800 mm wide VX IT network/server enclosures.
Benefits	Symmetrical or asymmetrical installation supported More space for cable routing or integration of a Liquid Cooling Unit (LCU) with one-sided, asymmetrical (laterally offset) installation Ideal for integrating 482.6 mm (19") mounting angles for alternative installation with 21", 23", or 24" components To boost the energy efficiency of an integral rack climate control system, the surrounding area around the 482.6 mm (19") mounting level can be covered with air baffle plates, enabling the more selective use of the cooling airflow and minimising exhaust airflows
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	Assembly parts
Load capacity	4000 N
Assembly instruction	It is attached directly onto the enclosure frame For screw-fastening the mounting angles to the cross members, a mounting bracket for VX IT 482.6 mm (19") mounting angles 5302169 is additionally required.
To fit	Width: = 800 mm
Packs of	2 pc(s).
Net weight	3.6

# Features

Gross weight	3.82
PCF per pack (cradle-to-gate)	14.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177955615
ETIM 9	EC002620
ECLASS 8.0	27189261