

Rittal – The System.

Faster – better – everywhere.



CP 6372.543 Comfort Panel

State: 2026.4.24 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6372.543 - Comfort Panel

Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability. Protection category IP 65 to IEC 60 529.



Features

| | |
|-----------------|--|
| Model No. | CP 6372.543 |
| Design | Support arm connection Ø 130 mm |
| Benefits | Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems |
| Material | Enclosure: Extruded aluminium section Corner pieces: Die-cast zinc Corner protectors: Plastic |
| General colour | Natural anodised |
| Colour | Enclosure: Natural anodised Corner pieces: RAL 7035 Corner protectors: similar to RAL 7024 |
| Supply includes | Enclosure with cut-out for support arm connection 3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C Seals and assembly parts for front panels Hinged rear panel, hinging on the longest side |

Features

| | |
|-------------------------------------|---|
| Dimensions | Width: 628.5 mm Height: 508.5 mm Depth: 209 mm |
| Installation depth | 191 mm |
| IP protection category to IEC 60529 | IP 65 |
| Protection category NEMA | NEMA 12 |
| To fit front panel width | 520 mm |
| To fit front panel height | 400 mm |
| Design | Servicing access from the rear |
| Note | The support arm connection may be swapped over by rotating the enclosure |
| Basic material | Aluminium |
| Lock | Lock version: Crescent-shaped cam Number of locks: 2 Lock insert: 3 mm double-bit |
| Packs of | 1 pc(s). |
| Net weight | 16.241 kg |
| Gross weight | 19.296 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002504 |
| ECLASS 8.0 | 27180505 |
| Product description | CP Compact Panel, for front panel BH 520x400 mm, installation depth 191 mm, Extruded aluminum section, Support arm connection Ø 130 mm, Screw-fastened rear panel |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK