

# Rittal – The System.

Faster – better – everywhere.



## DK 7200.630 Socket strip

State: 2025.7.20 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7200.630 - Socket strip in an aluminium duct

Socket strips in an aluminium duct, available in various lengths with different functional elements and variable attachment options.



## Features

Model No.	DK 7200.630
Product description	<p>The socket strips are available in various country-specific variants with different functional elements. Special attention has been devoted to practical, universal fastening: Variable attachment facilities have been created with an angle bracket which may be inserted in four positions. Hence, for example, the 482 mm long socket strips may optionally be mounted on 482.6mm (19") mounting angles, the 482.6 mm (19") mounting frame, on the enclosure frame, or in the rear section of the wall-mounted distributor. Socket strips with a length of more than 482 mm can only be fitted on the enclosure frame. The socket strip may be inserted into all sections with a 25 mm hole pattern, without the need for additional mounting accessories. This makes selection much easier, as well as providing additional flexibility and saving on warehousing. Provision has also been made for cable routing of the infeed, and when mounting in the 482.6 mm (19") section there is adequate space to route the infeed between the socket strip and the profile rail without kinks. The arrangement of the IEC 320 sockets at a 45° angle allows unrestricted use of angular connectors.</p>
Material	<p>Aluminium section, natural anodised</p> <p>Socket inserts: Polycarbonate</p>

# Features

Supply includes	Socket strip 2 mounting brackets Assembly parts
Dimensions	Height: 44 mm Depth: 44 mm
Length of connection cable	2 m
Connection cable (type)	H05VV-F3G1.5
Tolerance of mounting dimensions	25 mm
Rated operating voltage	230 V AC, 50 Hz
Rated voltage	230 V AC, 50 Hz
Note	Depending on the application, we recommend use of a charging current reserve to prevent incorrect activation due to starting-current spikes Variable attachment distance within a range of 25 mm, the distance given is hole centre – hole centre of mounting bracket
Packs of	1 pc(s).
Net weight	1.48
Gross weight	1.68
Customs tariff number	85366990
EAN	4028177206090
ETIM 9	EC000330
ECLASS 8.0	27142604

# Tender text

CMC Socket strip ,,,,,,,,,,

With integrated:

- Interference suppressor filter
- Overvoltage protection
- Signal contact

In case of occurring malfunctions due to overvoltage the connected active network components are protected. By means of the relay signal contact the undervoltage and malfunction due to overvoltage can be signalled via the CMC-TC in the network (SNMP Trap). Operational readiness is indicated by a green light in the strip. Another protection device is the interference filter which as a passive element protects the high-quality equipment.

Technical specifications:

Number of sockets: 9 pcs.  
Length of strip: 650 mm  
Rated voltage: 230 V AC, 50/60 Hz  
Rated current: 16 A  
Relay alarm output: RJ 10 jack  
Relay load capacity: 50 Volt DC 100 mA

Technical specifications overvoltage protection:

Arrester of utilization category: D  
Surge current resistance per conductor: 2.5 kA  
Maximum surge strength: 8kA