

# Rittal – The System.

Faster – better – everywhere.



## SK 7980.000 Fan expansion kit

State: 2026.7.1 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 7980.000 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

## Features

|   |   |
|---|---|
| Model No.   | SK 7980.000   |
| Product description   | For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate.  |
| Supply includes   | Fan<br>Connection cable (0.61 m)<br>Assembly parts  |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | At 50 Hz: 160 m <sup>3</sup> /h<br>At 60 Hz: 180 m <sup>3</sup> /h  |
| Rated operating voltage                                       | 230 V, 1~, 50 Hz/60 Hz  |
| Power consumption Pel   | At 50 Hz: 15 W<br>At 60 Hz: 14 W  |
| Dimensions  | Width: 119 mm<br>Height: 119 mm<br>Depth: 38 mm   |
| Operating temperature range                                   | -10 °C...55 °C  |
| Noise level   | At 50 Hz: 37 dB(A)<br>At 60 Hz: 37 dB(A)  |
| Packs of  | 1 pc(s).  |
| Net weight  | 0.6 kg  |
| Gross weight  | 0.671 kg  |
| Customs tariff number   | 84145915  |
| ETIM 9  | EC000320  |
| ECLASS 8.0  | 27180716  |
| Product description   | DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD: 119x119x38 mm, 230 V, 1 ~, 50/60 Hz |

# Tender text

Fan expansion kit for fan mounting plate

Rated operating voltage: 230V; Power consumption: 19/18

W at 50/60 Hz;

Air throughput (unimpeded air flow): 160 - 180 m<sup>3</sup>/h at  
50/60 Hz;

Temperature range: -10°C to +55°C

Dimensions (W x H x D): 119 mm x 119 mm x 38 mm