

Rittal – The System.

Faster – better – everywhere.



CP 6320.000

Command panels with handle strips

State: 2025.9.15 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6320.000 - Command panels with handle strips

Operating housings with modern sheet steel handle strips, with support arm cut-out Ø 130 mm to fit support arm system CP 60 / 120 / 180, service access optionally from the front or rear, aluminium front panel easily removable for machining, protection category IP 55.



Features

| | |
|-----------------|---|
| Model No. | CP 6320.000 |
| Material | Enclosure and door: Sheet steel Handle strips: Aluminium Front panel: Aluminium Cover caps: Plastic |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodised Front panel: Natural anodised |
| Colour | Enclosure and door: RAL 7035 Handle strip: Natural anodised Front panel: Natural anodised Cover caps: similar to RAL 7024 |
| Supply includes | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm Front with maximum cut-out, covered with easily machinable 3 mm aluminium front panel Side handle strips and cover caps Cam lock with 3 mm double-bit insert Integral interior installation bracket with TS system punchings |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 300 mm Height: 200 mm Depth: 155 mm |
| IP protection category to IEC 60529 | IP 55 |
| Design | Servicing access from the rear |
| Note | The support arm connection and door hinge may be swapped over by rotating the enclosure Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out Lock systems for servicing access from the rear: 27 mm lock inserts, type A, lock cylinder, plastic handles and T handles, type B |
| Basic material | Aluminium |
| Lock | Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit |
| Packs of | 1 pc(s). |
| Net weight | 4.29 |
| Gross weight | 4.38 |
| EAN | 4028177693975 |
| ECLASS 8.0 | 27180505 |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|