

Rittal – The System.

Faster – better – everywhere.



CX 6713.000 CX desk unit

State: 2025.9.3 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6713.000 - CX desk unit

Four widths form the bridge to two- or three-piece assembly of the CX console system.



Features

| | |
|-----------------|---|
| Model No. | CX 6713.000 |
| Design | Desk section |
| Material | Enclosure: Sheet steel 1.5 mm Console lid: Sheet steel 2.0 mm, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure Cover hinged at rear, 2 stays with automatic locking. Automatic unlocking on the left, manual unlocking on the right Opening for running cables into the enclosure base Lock: 3 mm double-bit Enclosure Cover hinged at bottom, including cover retainer Open base for individual cable entry |
| Dimensions | Width: 1,600 mm Depth: 745 mm |
| Height, front | 130 mm |
| Height rear | 200 mm |

Features

| | |
|-------------------------------------|---|
| IK Code | IK10 |
| Note | A cover plate is required to seal the desk unit A pedestal and a cover plate for desk unit are required for 2-part console assembly. A pedestal and desk unit are required for a 3-part console assembly. |
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Basic material | Sheet steel |
| Dimensions | Width: 1,600 mm |
| Number of locks | 3 |
| Lock version | Cam |
| Lock insert | 3 mm double-bit |
| Lock | Lock version: Cam Number of locks: 3 Lock insert: 3 mm double-bit |
| Packs of | 1 pc(s). |
| Net weight | 46 |
| Gross weight | 47 |
| Customs tariff number | 94032080 |
| EAN | 4028177983694 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

Approvals

Explanations

Declaration of conformity