

# Rittal – The System.

Faster – better – everywhere.



## DK 7827.180

## Mounting angles, 482.6 mm (19")

State: 2026.6.21 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7827.180 - Mounting angles, 482.6 mm (19") for TS, CS Toptec

Mounting angles in cranked design Mounting angles are available in an L-shape as an alternative.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | DK 7827.180   |
| Design                   | Cranked   |
| Benefits                 | Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level.   |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard)<br>Side round and square punchings<br>Clear chromated for conductive connection of the 482.6 mm (19") installed equipment.   |
| Material                 | Sheet steel, 2 mm   |
| Supply includes          | Assembly parts  |
| Dimensions               | Width: 482.6 mm   |
| Units                    | 38 U  |
| Note                     | The mounting angles can also be used to accommodate 21", 23" and 24" attachment dimensions.<br>Please select slide rails according to the relevant 482.6 mm (19") distance between levels.<br>If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used. |
| To fit                   | Enclosure type: TS 8<br>CS Toptec<br>Height: 1,800 mm   |
| Packs of                 | 2 pc(s).  |
| Net weight               | 5.266 kg  |
| Gross weight             | 5.543 kg  |
| Customs tariff number    | 73269098  |

# Features

---

|            |          |
|------------|----------|
| ETIM 9     | EC002620 |
| ECLASS 8.0 | 27189261 |

---

## Tender text

DK-TS mounting angle, 38 U

Technical specifications: 2 mm steel sheet, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated