Rittal – The System.

Faster – better – everywhere.



# SV 9340.050

# Busbar support

State: 2026.11.2 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9340.050 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

## Features

| | |
|---|---|
| Model No. | SV 9340.050 |
| Design | UL-certified |
| Material | Polyamide<br>Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Rated operating voltage | 1000 V, 3~<br>1500 V (DC) |
| Note on Model No. | The use of a base tray is required for UL applications |
| Electrical ratings UL (SCCR) | 14 kA - 600 V, support spacing 500 mm, 12 x 5/10 mm busbars<br>22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars<br>25 kA - 600 V, support spacing 250 mm, 12 x 5/10 mm busbars<br>25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars<br>30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars<br>50 kA - 600 V, support spacing 350 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7<br>54 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7<br>65 kA - 480 V, support spacing 250 mm, 30 x 5/10 mm busbars, circuit breaker max. 600 A, DIVQ/7<br>73 kA - 600 V, support spacing 250 mm, 30 x 5/10 mm busbars, Fuse Class L max. 800 A, JDDZ/7 |
| Number of poles | 3-pole |

© Rittal 2026

# Features

| | |
|---|---|
| To fit Model No. | 3580000<br>3581000<br>3582000<br>3583000<br>3584000<br>3580100<br>3581100<br>3585005<br>3586005 |
| Internal attachment | Yes |
| Centre-to-centre spacing of busbars | 60 mm |
| To fit busbars | 12 x 5 - 30 x 10 |
| Packs of | 4 pc(s). |
| Net weight | 0.668 kg |
| Gross weight | 0.72 kg |
| Customs tariff number | 85469010 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |
| Product description | SV Busbar support, 3-pole, 60 mm centre-to-centre spacing, for busbar WxH: 12x5-30x10 mm, UL version |

# Approvals

| | |
|---|---|
| Approvals | ABS<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

UL busbar support
UL busbar support with internal attachment, 3-pole
Technical specifications
Bar centre distance: 60 mm
Busbars E-Cu, 15 x 5 to 30 x 10 mm
Construction width: 20 mm
Length: 190 mm
Note
The use of a base tray is compulsory for
UL applications.
System:
Rittal RiLine60

© Rittal 2026