

Rittal – The System.

Faster – better – everywhere.



TS 8612.080

**TS punched section with mounting
flange, 17 x 73 mm**

State: 2026.7.7 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.080 - TS punched section with mounting flange, 17 x 73 mm

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

| | |
|----------------------|--|
| Model No. | TS 8612.080 |
| Design | For the inner mounting level and for mounting on doors |
| Product description | For universal skeleton structures or partial assembly. Simply locate into the punchings and secure. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly screws |
| Length | 790 mm |
| To fit door width | 900 mm |
| Installation options | On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round For SE, may additionally be mounted on the top horizontal section in the depth In the tubular door frame for TS, SE and PC In TP via rail for interior installation: In the width, for inner mounting level As a mounting kit for component shelves in TS, VX SE, simply locate and secure |
| Assembly instruction | The rail for internal mounting is required when installing in TP |

Features

| | |
|-------------------------------|---|
| To fit | Enclosure type: VX SE TP PC IW TX CableNet Width/depth: 800 mm |
| Packs of | 4 pc(s). |
| Net weight | 3.384 kg |
| Gross weight | 3.54 kg |
| PCF per pack (cradle-to-gate) | 13.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS punched section with mounting flange, 17 x 73 mm, for inner mounting level: for W/D: 800 mm, for door width: 900 mm, L: 790 mm |