Rittal – The System.

Faster - better - everywhere.





SV 9340.930 OM adaptors

State: 2025.11.17 (Source: rittal.com/lt-en)



SV 9340.930 - OM adaptors with plug-in cable outlet



Features

Model No.	SV 9340.930
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Supply includes	Connector with connection facility for 3 main contacts (1.5 – 4 mm²)
Rated current max.	25 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, 1 x TS 55D, 1 x TS 55D-V
Number of poles	3-pole
Connector outlet	Connector with connection facility for 3 main contacts (1.5 – 4 $$ mm ²)
Dimensions	Width: 55 mm Height: 208 mm
Connection of round conductors	1.5 - 4 mm²
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 170 mm

© Rittal 2025

Features

1 pc(s).
• •
0.3
0.332
0.025
85369095
4028177555471
EC001531
EC001531
27370304

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3

Tender text

OM adaptor 25 A premium

OM adaptor 25 A premium, 3-pole

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 208 mm

Support frame: 55x 170 mm

Support frame support: -

PinBlock: -

Connector outlet: with connection facility

for 3 main contacts

Support rail: -

System:

Rittal RiLine60

© Rittal 2025 4