

Rittal – The System.

Faster – better – everywhere.



SV 9340.930 OM adaptors

State: 2026.2.8 (Source: ittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.930 - OM adaptors with plug-in cable outlet



Features

| | |
|---|---|
| Model No. | SV 9340.930 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| Supply includes | Connector with connection facility for 3 main contacts (1.5 – 4 mm ²) |
| Rated current max. | 25 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with centre-to-centre spacing | 60 mm |
| Support rail type | Support frame, 1 x TS 55D, 1 x TS 55D-V |
| Number of poles | 3-pole |
| Connector outlet | Connector with connection facility for 3 main contacts (1.5 – 4 mm ²) |
| Dimensions | Width: 55 mm Height: 208 mm |
| Connection of round conductors | 1.5 - 4 mm ² |
| Support rails Qty/height | 2 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Support frame (W x H) | 55 mm x 170 mm |

Features

| | |
|------------------------------|---------------|
| Packs of | 1 pc(s). |
| Net weight | 0.3 |
| Gross weight | 0.332 |
| Copper weight (kg per piece) | 0.025 |
| Customs tariff number | 85369095 |
| EAN | 4028177555471 |
| ETIM 9 | EC001531 |
| ETIM 8 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

OM adaptor 25 A premium

OM adaptor 25 A premium, 3-pole

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 55 mm

Length: 208 mm

Support frame: 55x 170 mm

Support frame support: -

PinBlock: -

Connector outlet: with connection facility

for 3 main contacts

Support rail: -

System:

Rittal RiLine60