

Rittal – The System.

Faster – better – everywhere.



SV 9342.300 Connection adaptor

State: 2026.5.8 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.300 - Connection adaptor

For bar systems with 60 mm centre-to-centre spacing.

Features

Model No.	SV 9342.300
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated current max.	800 A
Rated operating voltage	690 V, 3~
Electrical ratings UL (SCCR)	50 kA - 600 V, Fuse Class K5 max. 600 A, JDDZ/7 65 kA - 480 V, circuit breaker max. 600 A, DIVQ/7 65 kA - 600 V, Fuse Class L max. 800 A, JDDZ/7
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Note	The technical data may vary for UL applications UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar supports 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 129 mm Height: 246 mm
Connection of round conductors, fine wire with wire end ferrule	95 - 185 mm ²
Connection of round conductors, multi-wire	95 - 300 mm ²
To fit busbars	Height: 5, 10 mm

Features

Clamping area for laminated copper bars (W x H)	33 x 20 mm
Rated operating voltage (L1 + L2)	1000 V (DC)
Rated operating voltage (L1 + L3)	1500 V (DC)
Approvals	UL
For bar thickness	10 mm
Packs of	1 pc(s).
Net weight	1.365 kg
Gross weight	1.58 kg
Copper weight (kg per piece)	0.358
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Connection adaptor, 800 A, 690 V, 3-pole, cable outlet bottom, round conductor connection 95-300 mm ² , clamping area WH: 33x20 mm

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Connection adapter 800 A

Connection adaptor 800 A, 3-pole,
cable outlet at the bottom

for busbar thickness 5/10 mm and PLS 800/1600

Type of connection

Round conductor, fine wire with wire end ferrule:

95 - 185 qmm

Round conductor, multi-wire: 95 - 300 qmm

Clamping area for laminated copper bar:

33 x 20 mm

For UL applications: AWG 3/0 - MCM 600

System:

Rittal RiLine60