
Rittal – The System.

Faster – better – everywhere.



# SV 9345.720

# Circuit-breaker component adaptor

State: 2026.10.31 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9345.720 - Circuit-breaker component adaptor 3-pole

Circuit-breaker adaptor for universal, simplified assembly of circuit-breakers.



## Features

| | |
|---|---|
| Model No. | SV 9345.720 |
| Material | Polyamide<br>Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Connection straps<br>Sliding blocks |
| Rated current max. | 400 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear<br>The technical data may vary for UL applications |
| Electrical ratings UL (SCCR) | 65 kA - 480 V, circuit breaker max. 400 A, DIVQ/7 |
| Cable outlet | Top |
| For bar systems with centre-to-centre spacing | 60 mm |
| Number of poles | 3-pole |
| Dimensions | Width: 140 mm<br>Height: 345 mm |
| To fit busbars | Height: 5, 10 mm |

© Rittal 2026

# Features

| | |
|---|---|
| To fit manufacturer (model) | Eaton (NZM3, NZM3 UL/400 A)<br>GE (FG400)<br>Mitsubishi (NF400-SEW/HEW/REW)<br>Schneider Electric (NS(X)400, NSJ400)<br>Schrack (MC3)<br>Siemens (VL400, VL400X UL, VL400 UL, 3VA23, 3VA63)<br>Terasaki (E400, S400, H400, L400) |
| Approvals | UL |
| Packs of | 1 pc(s). |
| Net weight | 2.88 kg |
| Gross weight | 2.98 kg |
| Copper weight (kg per piece) | 1.533 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 400 A, 690 V, 3-pole, cable outlet top, with connection straps |

# Approvals

| | |
|---|---|
| Approvals | ABS<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |