Rittal – The System.

Faster – better – everywhere.



# VX 8660.023

# Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 2026.11.11 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 8660.023 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces with trim panels for flexible cable entry.





## Features

| | |
|---|---|
| Model No. | VX 8660.023 |
| Benefits | Reliable – Excellent stability of the base/plinth<br>Flexible – Countless interior installation options with VX accessories<br>Simple – Flush termination between the baying points |
| Material | Base/plinth corner piece: Sheet steel<br>Base/plinth trim panel front/rear: Sheet steel<br>Corner and baying cover: Plastic |
| Colour | RAL 9005 |
| Supply includes | 4 corner covers<br>Assembly parts<br>4 base/plinth corner pieces, 200 mm high<br>1 base/plinth trim panel, front/rear, 200 mm high<br>2 base/plinth trim panels, front/rear, 100 mm high |
| Note | Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Height: 200 mm |
| To fit | Enclosure type: VX<br>VX IT<br>VX SE<br>TX CableNet<br>TS<br>TS IT<br>TP<br>PC<br>IW<br>CX<br>Width: = 800 mm |
| Type rating to 508A | Type 1<br>Type 12 |
| Weight/pack | 8.68 kg |
| Packs of | 2 pc(s). |
| Net weight | 8.28 kg |
| Gross weight | 8.687 kg |
| PCF per pack (cradle-to-gate) | 30.51 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX base/plinth corner piece with trim panel, front and rear, H: 200 mm, for W: 800 mm, sheet steel |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL - FTTA |

# Approvals

| | |
|---|---|
| Explanations | PCF-declaration |