


Rittal – The System.

Faster – better – everywhere.



RX 9360.150 RiLineX basic module

State: 2025.6.5 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.150 - RiLineX basic module

Board module, 3-pole, 54 mm wide, including busbar support and contact hazard protection cover.

Features

Model No.	RX 9360.150
Benefits	Scalable system lengths with basic modules Simple assembly Scalable rated currents thanks to variable busbar cross-sections Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Extensive range of system accessories Contact hazard protection up to IP 2XB, upgradable to IP 4X Tested and certified to IEC and UL Simple extension and baying
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 35745 RAL 9005
Supply includes	Basic module base section Basic module (contact hazard protection cover) Assembly screws
IP protection category to IEC 60529	IP 2XB
Standards	IEC/EN 61439-1 UL 508
Rated current max.	800 A
Note	Busbars are not included with the supply
Electrical ratings UL (SCCR)	65 kA - 600 V, RMS 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7

Features

Centre-to-centre spacing of busbars	60 mm
Rated impulse withstand voltage U _{imp}	12 kV
Rated voltage	1,000 V AC 600 V AC (UL) 1,500 V DC 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated short-term withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 54 mm Height: 246 mm Depth: 49 mm
Packs of	6 pc(s).
Net weight	1.56
Gross weight	1.92
Customs tariff number	85369010
EAN	4028177997271

Features

ETIM 9	EC001900
--------	----------

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity