Rittal – The System.

Faster – better – everywhere.



VX 8660.120

Levelling component

State: 2026.11.1 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8660.120 - Levelling component for base/plinth system VX, sheet steel

For retrospective levelling on uneven floors at the installation site up to a maximum of 15 mm. Installed through the base/plinth corner piece.



Features

Model No.	VX 8660.120
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Load capacity	Max. admissible load: 2500 N per levelling component
Note	For use in combinations of VX, VX IT, VX SE, TX , TS, TS IT, PC, IW, TP with the base/plinth system VX Check the load capacity of the floor.
Dimensions	Height: 100 mm
Weight/pack	0.612 kg
Packs of	4 pc(s).
To fit	for base/plinth system VX, sheet steel
Net weight	0.56 kg
Gross weight	0.611 kg
Customs tariff number	73181900
ETIM 9	EC004043
ETIM 8	EC000721

© Rittal 2026

Features

ECLASS 8.0	27182003
Product description	VX levelling component for base/plinth system VX, H: 100 mm