

Rittal – The System.

Faster – better – everywhere.



RX 9360.805

RiLineX bus-mounting fuse base

State: 2026.2.13 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9360.805 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With electronic and optical LED fuse monitoring via alarm contacts. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable in the open state and sealable in the closed state. A spring terminal block up to 16 mm² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free snap-on mounting and has semi-automatic rail adjustment for 5 and 10 mm.



Features

Model No.	RX 9360.805
Design	with electronic fuse monitoring
Benefits	<p>Reliable contacting of fuse inserts (without screw caps)</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Optical LED fuse monitoring</p> <p>Voltage test through separate opening</p> <p>Maintenance-free tension spring connection up to 16 mm²</p> <p>Complete contact hazard protection without any additional accessories (such as screw caps)</p>
Product changes	(secondary)
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94-V0</p>
Colour	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	<p>4 bus-mounting fuse bases</p> <p>12 reducers for D 01 fuses</p>
Rated current max.	63 A

Features

Cable outlet	Bottom
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 35.8 mm Height: 253.8 mm Depth: 89.8 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 16 mm ²
Connection of round conductors, fine wire with AWG wire end ferrule	AWG 16 - AWG 6
Connection of round conductors, multi-wire	1.5 - 16 mm ²
Connection of round conductors, multi-wire mm ²	AWG 16 - AWG 6
To fit busbars	Height: 5, 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Overvoltage category	4
Contamination level	3
Standards	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	1,000 V
Power dissipation (max.)	5.5 W
IP protection category to IEC 60 529	IP 2XB
Operation humidity max.	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C

Features

Ambient humidity (non-condensing) 10...90 %

Utilisation category AC-21B (400 V/100 A)

Fuse inserts D 02-E 18

Packs of 4 pc(s).

Net weight 1.796

Gross weight 1.8

Copper weight (kg per piece) 0.07

Customs tariff number 85369095

ETIM 9 EC001644

Approvals

Explanations Declaration of conformity