Rittal – The System.

Faster – better – everywhere.





KEL 9306.000 Ex enclosures

State: 2025.11.2 (Source: rittal.com/lt-en)



KEL 9306.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel







Features

Model No.	KEL 9306.000	
Design	Ex enclosures	
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC	
	Ambient temperature range: -30 °C+80 °C	
	The specified temperatures may be limited by the installed equipment	
	Explosion protection category to EN 60 079: Equipment protection	
	thanks to increased safety (Ex e), equipment protection thanks to	
	enclosure (Ex tb)	
Material	Enclosure: Stainless steel 1.4301 (AISI 304)	
	Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in	
	silicone seal	
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 μm	
Supply includes	Enclosure	
	Cover	
Dimensions	Width: 300 mm	
	Height: 300 mm	
	Depth: 120 mm	

© Rittal 2025

Features

Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60 529	IP 66
Packs of	1 pc(s).
Net weight	3.7
Gross weight	3.9
Customs tariff number	94032080
EAN	4028177138643
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX	
	ATEX QA	
	IECEx	
	IECEx QAR	

© Rittal 2025 3