

Rittal – The System.

Faster – better – everywhere.



SV 9340.004 Busbar support

State: 2026.6.9 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.004 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

Features

| | |
|------------------------------|--|
| Model No. | SV 9340.004 |
| Design | UL-certified |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Rated operating voltage | 1000 V, 3~ |
| Electrical ratings UL (SCCR) | 22 kA - 600 V, support spacing 500 mm, 15 x 5 - 25 x 10 mm busbars 25 kA - 600 V, support spacing 500 mm, 30 x 5/10 mm busbars 30 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars 65 kA - 600 V, support spacing 250 mm, 15 x 5 - 25 x 10 mm busbars, Fuse Class L max. 800 A, JDDZ/7 |
| Note on Model No. | If 12 x 5/10 mm busbars are used, spacer 9340.090 is additionally required The use of a base tray is required for UL applications UL approval only applies in conjunction with AC application |
| Number of poles | 4-pole |
| To fit Model No. | 3580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005 |
| Internal attachment | Yes |

Features

| | |
|-------------------------------------|---|
| Centre-to-centre spacing of busbars | 60 mm |
| To fit busbars | 12 x 5 - 30 x 10 |
| Packs of | 4 pc(s). |
| Net weight | 0.84 kg |
| Gross weight | 0.915 kg |
| Customs tariff number | 85469010 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |
| Product description | SV Busbar support, 4-pole, 60 mm bar centre distance, for busbar WH: 12x5-30x10 mm, UL design |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
