

Rittal – The System.

Faster – better – everywhere.



PK 9520.000

Polycarbonate enclosures PK

State: 2026.6.27 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9520.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

| | |
|-----------------------------------|---|
| Model No. | PK 9520.000 |
| Design | PK enclosure with solid cover |
| Product description | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment. |
| Material | Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover Cover screws Insulating bungs for wall mounting screws |
| Protection category NEMA | NEMA 4X |
| Protection category to IEC 60 529 | IP 66 |
| IK Code | IK08 |

Features

| | |
|-----------------------------|---|
| Dimensions | Width: 254 mm Height: 180 mm Depth: 90 mm |
| Operating temperature range | -35 °C...80 °C |
| Basic material | Polycarbonate |
| Packs of | 1 pc(s). |
| Net weight | 0.713 kg |
| Gross weight | 0.813 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | PK Polycarbonate enclosure, WHD: 254x180x90 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover |

Approvals

| | |
|--------------|---------------------------|
| Approvals | C-UL DNV UL |
| Explanations | Declaration of conformity |

Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate
without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate
all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 254 x 180 x 90 mm