

Rittal – The System.

Faster – better – everywhere.



RX 9360.000

RiLineX baying set

State: 2026.2.11 (Source: [ittal.com/it-en](https://www.ittal.com/it-en))



RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.



Features

Model No.	RX 9360.000
Benefits	<p>Time savings thanks to fully digital product data</p> <p>Reduced assembly time thanks to pre-assembled complete board</p> <p>Tested short-circuit resistance up to 65 kA</p> <p>Suitable for applications up to 1000 V AC and up to 1500 V DC</p> <p>Tested and certified to IEC and UL</p> <p>Simple extension and baying</p>
Material	<p>Upper part: Sheet steel, zinc-plated</p> <p>Contact plate: E-Cu, tin-plated</p> <p>Front cover: Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	RAL 35745
Supply includes	<p>3 busbar connectors</p> <p>1 front cover</p> <p>1 insulating plate</p>
IP protection category to IEC 60529	IP 2XB
Standards	<p>IEC 61 439-1/-2</p> <p>UL 508</p>

Features

Rated current max.	780 A
Rated current (UL)	780 A
Electrical ratings UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Rated impulse withstand voltage Uimp	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage Ui	1,000 V AC 1,500 V DC
Rated impulse withstand current	103 kA 115.5 kA
Rated short-term withstand current/t	45 kA/200 ms 52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	30 x 5/10
Operating temperature range	-5 °C...55 °C
Dimensions	Width: 154 mm Height: 240 mm Depth: 77 mm
Packs of	1 pc(s).
Net weight	1.88

Features

Gross weight	1.924
Copper weight (kg per piece)	0.297
Customs tariff number	85369010
EAN	4028177997431
ETIM 9	EC002270

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
