

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.915 Connection block

State: 2026.5.29 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.915 - Connection block

For connecting cables and laminated copper bars.

## Features

Model No.	SV 9677.915
Product description	For connecting cables and laminated copper bars.
Material	Sheet steel, zinc-plated E-Cu, tin-plated
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated current max.	1,000 A
Dimensions	Width: 98 mm
Connection of round conductors	185 - 300 mm <sup>2</sup>
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Net weight	1.2 kg
Gross weight	1.35 kg
Copper weight (kg per piece)	0.893
PCF per pack (cradle-to-gate)	5.1 kg CO <sub>2</sub> eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection block, 1000 A, 690 V, 1-pole, cable outlet top/bottom, round conductor connection 185-300 mm <sup>2</sup>

# Approvals

---

Approvals

UL + C-UL (listed)

---

Explanations

Declaration of conformity

Declaration of conformity UK