

Rittal – The System.

Faster – better – everywhere.



RX 9360.525

RiLineX CB component adaptor

State: 2026.5.21 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

RX 9360.525 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 145 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Model No.	RX 9360.525
Design	Easy Fix
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	3 terminal covers
IP protection category to IEC 60529	IP 2XB

Features

Rated impulse withstand voltage Uimp	8 kV
Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage Ui	1,000 V
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Cross-section	29 mm ² 6 mm ²
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 145 mm Height: 325.8 mm
Packs of	1 pc(s).
Net weight	4 kg
Gross weight	4.298 kg
Copper weight (kg per piece)	1.652
PCF per pack (cradle-to-gate)	19.01
Customs tariff number	85369095

Features

ETIM 9	EC001531
--------	----------

Product description	RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. The cable outlet is easily converted to the top or bottom to suit individual requirements.
---------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Explanations	Declaration of conformity PCF-declaration
--------------	----------------------------------------------

Tender text

RiLineX CB component adaptor (Easy-Fix)

RiLineX CB component adaptor
for 60 mm busbar systems.

The switch mounting pattern is easily
adjusted for fastening using two
adjustment discs integrated into the adapter.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 400 A

Connection: 174 mm²

Cable outlet: top/bottom

Dimensions: 145 mm x 325 mm x 76 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360525