

Rittal – The System.

Faster – better – everywhere.



RX 9360.500

RiLineX CB component adaptor

Estado: 11/09/2025 (Fuente: rittal.com/mx-es)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.500 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

Características

Referencia	RX 9360.500
Ejecución	Easy Fix
Ventajas	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamida (PA 6) Protección frente al fuego según UL 94
Color	RAL 9005 RAL 35745
Unidad de envase	3 connection space covers
Grado de protección IP según IEC 60 529	IP 2XB
Tensión asignada soportada al impulso Uimp	12 kV
Tensión nominal	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Rated impulse withstand current	80 kA
Categoría de sobretensión	4

Características

Grado de suciedad	3
N° de polos	3 polos
Salida de cables	abajo
Tipo de conexión (eléctrica)	Borne
Adecuado para el fabricante (tipo)	ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160) BTicino (M1 160) Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160) Eaton (NZM1) Fuji Electric (BW125JAG-3P) Hager (P160) Himel (HDM3-100F/N, HDM3L-125) Hyundai Electric (100AF, 125AF, 125D, 160D AF) Legrand (DPX 160, DPX 250 ER, DPX ³ 160) LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160) Mitsubishi (NF63-SV, NF125-SV) OEZ (BC160) Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16) Sassin (3SM8L-100) Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100) Schrack (MC1) Siemens (3VA10, 3VA11) Terasaki (E125, S125)
Adecuado para sistema de barras colectoras	RiLineX RiLine60
Frecuencia fundamental	50...60 Hz
Humedad del aire (sin condensación)	10...90 %
Adecuado para barras colectoras	15 x 5/10 20 x 5/10 30 x 5/10
Campo de temperatura de servicio	-25 °C...55 °C
Campo de temperatura de almacenaje	-25 °C...75 °C

Características

Dimensiones	Anchura: 81 mm Altura: 252 mm Profundidad: 63 mm
Unidad de embalaje	1 pza(s).
Peso neto	1.364
Peso bruto	1.367
Contenido de cobre (kg / pza.)	0.375
Código arancelario	85369095
EAN	4028177997158
ETIM 9	EC001531

Aprobaciones

Aprobaciones	UL + C-UL (listed)
--------------	--------------------