Rittal - The System.

Faster – better – everywhere.





RX 9363.110 RiLineX NH fuse-switch disconnector

State: 2025.12.13 (Source: rittal.com/lt-en)



RX 9363.110 - RiLineX NH fuse-switch disconnector

RiLineX NH fuse-switch disconnector in size 1 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection.



Features

RX 9363.110
For mounting plate assembly
Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
RAL 9005 RAL 35745
Yes
Top/bottom
Screw M10
1,000 kV
250 A
250 A
690 V AC

© Rittal 2025 2

Features

For NH size	1
Test specification	IEC/DIN EN 60 947-3
	DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 181.8 mm
	Height: 298 mm
	Depth: 110.5 mm
Operating temperature range	-5 °C35 °C
Storage temperature range	-25 °C70 °C
Number of poles	3-pole
Utilisation category	AC-23B (400 V/100 A)
	AC-22B (500 V/100 A)
	DC-22B (250 V/100 A)
	DC-21B (440 V/100 A)
Contamination level	3
IP protection category to IEC 60 529	IP 2XB
Fire load	33.55 MJ/m²
Power dissipation (max.)	42 W
Packs of	1 pc(s).
Net weight	2.2
Gross weight	2.209
Copper weight (kg per piece)	0.57
Customs tariff number	85369095
ETIM 9	EC001040

Approvals

ty

© Rittal 2025 3