

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.655

# Apparathyller, fast montering

Stat: 26.06.2026 (Kilde: [rittal.com/no-no](http://rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.655 - Apparathyller, fast montering for VX IT, TS IT, TE, TX CableNet

For fast montering mellom to 19"-montasjenivåer.

## Funksjoner

|                         |  |
|-------------------------|--|
| Art.nr                  | DK 5501.655  |
| Fordeler                | Én-manns tidsbesparende montering uten verktøy   |
| Anvendelsesområder      | Dybdevariabel for tilpasning til individuelle nivåavstander  |
| Materiale               | Stålplate  |
| Overflate               | Lakkert  |
| Farge                   | RAL 9005   |
| Leveringsomfang         | Inkl. festemateriell   |
| Monteringsmuligheter    | 19" (482,6 mm) - L-profilskinner foran og bak<br>19" (482,6 mm)-montasjerammer foran og bak                      |
| Anvendelsesområder      | Ved større nivåavstander er det nødvendig å redusere den forhåndsmonterte nivåavstanden, kan belastes med 50 kg. |
| Belastning              | 50 kg  |
| Dimensjoner             | Bredde: 484 mm   |
| Passer for              | Kapslingstype: VX IT<br>TS IT<br>TE<br>TX CableNet   |
| Nivå-avstand            | 400 - 600 mm   |
| Pakkeenhet              | 1 stk.   |
| Nettovekt               | 4,5 kg   |
| Bruttovekt              | 4,82 kg  |
| PCF/VE (Cradle-to-Gate) | 25 kg CO2 eq (Cat B)   |

# Funksjoner

|                                |  |
|--------------------------------|--|
| Merknad som gjelder PCF-klasse | Kategori B: PCF-verdi (Cradle-to-Gate) omtrentlig beregnet på grunnlag av produktets vekt og selvdeklart |
| Tolltariffnummer               | 73269098   |
| ETIM 9                         | EC002620   |
| ECLASS 8.0                     | 27189261   |
| Produktbeskrivelse             | DK Apparathyller, BxH: 484 mm x 0,5 HE, 50 kg, nivå-avstand: 400-600 mm, dybdevariabel , RAL 9005        |