

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.665

# Apparathyller, fast montering

Stat: 06.05.2026 (Kilde: [rittal.com/no-no](http://rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.665 - Apparathyller, fast montering for VX IT, TS IT, TE, TX CableNet

For fast montering mellom to 19"-montasjenivåer.

## Funksjoner

Art.nr	DK 5501.665
Fordeler	Én-manns tidsbesparende montering uten verktøy
Anvendelsesområder	Dybdevariabel for tilpasning til individuelle nivåavstander
Materiale	Stålplate
Overflate	Lakkert
Farge	RAL 9005
Leveringsomfang	Inkl. festemateriell
Monteringsmuligheter	19" (482,6 mm) - L-profilskinner foran og bak 19" (482,6 mm)-montasjerammer foran og bak
Belastning	50 kg
Dimensjoner	Bredde: 484 mm
Passer for	Kapslingstype: VX IT TS IT TE TX CableNet
Nivå-avstand	600 - 900 mm
Pakkeenhet	1 stk.
Nettovekt	6,47 kg
Bruttovekt	6,62 kg
PCF/VE (Cradle-to-Gate)	17,7 kg CO2 eq (Cat B)
Merknad som gjelder PCF-klasse	Kategori B: PCF-verdi (Cradle-to-Gate) omtrentlig beregnet på grunnlag av produktets vekt og selvdeklart
Tolltariffnummer	73269098

# Funksjoner

---

ETIM 9	EC002620
ECLASS 8.0	27189261
Produktbeskrivelse	DK Apparathyller, BxH: 484 mm x 0,5 HE, 50 kg, nivå-avstand: 600-900 mm, dybdevariabel , RAL 9005

---