Rittal - The System.

Faster – better – everywhere.





SR 2338.235 Swing frame, large, with trim panel

State: 17/11/2025 (Source: rittal.com/nz-en)



SR 2338.235 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.



Features

Model No.	SR 2338.235
Design	482.6 mm (19") level, centre
Product description	For mounting 482.6 mm (19″) equipment.
Material	Sheet steel
Surface finish	Frame: Zinc-plated
	Trim panel: Spray-finished
Colour	RAL 7035
Supply includes	Locking rod system with double-bit lock insert
	Material for attaching
Installation options	In the TS/SE with 180° opening angle
Assembly instruction	Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required

© Rittal 2025 2

Features

Note	For further installation options, see "Technical details" For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock
To fit	Enclosure type: TS VX SE Width: = 800 mm Height: ≥ 1,800 mm
Units	36 U
To fit enclosure type	TS VX SE
Packs of	1 pc(s).
Net weight	19.105
Gross weight	20.11
Customs tariff number	94039910
EAN	4028177165182
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3

Tender text

Large swing frame for network enclosure

36 U can be used for accommodating 482.6 mm (19") equipment. Torsionally stiff frame, welded from rectangular tube and triple folded support section. Load capacity up to 1500 N when standard hinges are used. Distance from inside edge of door to front edge of swing frame 100 mm, may be installed deeper on a pitch pattern of 25 mm. The swing frame must be fitted to the left / to the right depending on the installation depth of the equipment.

Installation position of equipment mounted in the centre.

Material: sheet steel

Surface finish: RAL 7035

for enclosure width: W: 800 mm

© Rittal 2025 4