

**Rittal – The System.**

Faster – better – everywhere.



# SM 2384.040

## Switch housings

State: 29/06/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 2384.040 - Switch housings Stainless steel

Switch housing made from stainless steel 1.4301 (AISI 304) with switch cut-outs, diameter: 22.5 mm. Protection category IP 66.

## Features

Model No.	SM 2384.040
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Enclosure and cover: Brushed, grain 240
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 280 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Pitch pattern	60 mm
Cut-outs (quantity x diameter)	4 x 22.5 mm
Lock	Lock version: Quick-release fastener including plastic bushes Number of locks: 4
Cable entry (quantity x diameter)	4
No. of metric knockouts	4
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	1.4 kg

# Features

---

Gross weight	1.501 kg
PCF per pack (cradle-to-gate)	5.1
Customs tariff number	84879090
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	SM Switch housing, WHD: 280x100x90 mm, Stainless steel 1.4301, without mounting plate, 4 switch cut-outs

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration
--------------	--