


# Rittal – The System.

Faster – better – everywhere.



## HD 2410.011 Cable gland HD

State: 8/09/2025 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 2410.011 - Cable gland HD

More compact design and the lock nut is included with the supply.



## Features

Model No.	HD 2410.011
Design	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the depositing of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Manufacturer Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

# Features

IP protection category to IEC 60529	IP69 / IPX8 (5 bar, 30 min)
Packs of	5 pc(s).
Net weight	0.1
Gross weight	0.2
Customs tariff number	73072980
EAN	4028177928718
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

# Approvals

Approvals	UR + C-UR (recognized) VDE
-----------	-------------------------------