

Rittal – The System.

Faster – better – everywhere.



SV 9635.382 Component adaptor

State: 2026.3.28 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.382 - Component adaptor 1-pole

For assembly of switchgear and protective gear.

Features

Model No.	SV 9635.382
Design	L2
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 7035
Note	Different adaptor versions are required depending on the preferred phase connection The technical data may vary for UL applications
Rated current max.	63 A
Rated operating voltage	690 V (AC), 1~
Number of poles	Single-pole
Connection cables (AWG)	AWG 8
Length of connection cable	100 mm
Support rails Qty/height	1 / 10 mm
Support rail type	static
Dimensions	Width: 18 mm Height: 160 mm Depth: 35 mm
Packs of	6 pc(s).
Net weight	0.36 kg
Gross weight	0.462 kg
Copper weight (kg per piece)	0.021

Features

Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV component adaptor 63 A, 690 V (AC), 1-pole (variant L2), connection cable AWG 8, WH: 18 x 160 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
