


Rittal – The System.

Faster – better – everywhere.



RX 9360.008 RiLineX-board

Staat: 2-11-2025 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.008 - RiLineX-board

Compleet board 800 A, 905 mm voor 1000 mm brede kasten/behuizingen.

Functies

Bestelnr.	RX 9360.008
Voordelen	Time savings thanks to fully digital product data Reduced assembly time thanks to pre-assembled complete board Suitable for applications up to 1000 V AC and up to 1500 V DC Tested short-circuit resistance up to 65 kA Contact hazard protection up to IP 2XB, upgradable to IP 3X Tested and certified to IEC and UL Simple extension and baying
Materiaal	Polyamide (PA 6) Vlamdovend volgens UL 94 E-Cu
Kleur	RAL 35745 RAL 9005
Levering	Incl. geïntegreerd railkoper
Beschermklasse IP volgens IEC 60 529	IP 2XB
Normen	IEC 61 439-1/-2 UL 508
Nominale stroom max.	800 A
Nominale stroom (UL)	800 A
Elektrische waarden UL (SCCR)	65 kA - 600 V, RMS 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, Circuit Breaker max. 600 A, DIVQ/7 100 kA - 480 V, Circuit Breaker max. 800 A, DIVQ/7 65 kA - 600 V, Circuit Breaker max. 800 A, DIVQ/7
Hartafstand systeemstroomrails	60 mm
Nominale stoothoudspanning Uimp	12 kV

Funcities

Nominale spanning	1.000 V AC 1.500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage	1.000 V AC 1.500 V DC
Rated impulse withstand current	143 kA 143 kA (UL)
Nominale kortsluitstroomvastheid/ t	65 kA/500 ms
Overspanningscategorie	4
Vervuilingsgraad	3
Railkoperafmetingen	30 mm x 10 mm
Aantal polen	3-polig
Frequentie van de grondgolf	50...60 Hz
Luchtvochtigheid (niet condenserend)	10...90 %
Bedrijfstemperatuurbereik	-5 °C...55 °C
Opslagtemperatuurbereik	-25 °C...75 °C
Afmetingen	Breedte: 905 mm Hoogte: 246 mm Diepte: 49 mm
Leveringseenheid	1 st.
Nettogewicht	11.5
Brutogewicht	12.032
Koperaandeel (kg / stuk)	7.224
Douanetariefnummer	85369010
EAN	4028177997417
ETIM 9	EC001900

Goedkeuringen

Goedkeuringen

UL + C-UL (listed)

Verklaringen

Verklaring van conformiteit