

Rittal – The System.

Faster – better – everywhere.



AS 4055.474

Hullplatemaskin Sub-D

Stat: 20.12.2025 (Kilde: [rittal.com/no-no](https://www.rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.474 - Hullplatemaskin Sub-D for stålplate og rustfritt stål

For utstansing av rettvinklede utsparinger for pluggforbindelse

Funksjoner

Art.nr	AS 4055.474
Produktbeskrivelse	For utstansing av rettvinklede utsparinger for pluggforbindelse. Hullplatemaskinen betjenes med skiftnøkkel eller hydraulikkstanseverktøy.
Fordeler	Med utkast på siden for avfallsstykket Matrisen blir ikke fastklemt Som trekkbolter blir det brukt vridningssikre aksler for stempel og matrise
Leveringsomfang	Matrise Stempel Trekkbolt Kontramutter Trykkmutter med kulelager Adapter for hydraulikk Plastkoffert
Materiale som kan bearbeides	Stålplate Rustfritt stål
Maks. bearbeidbar materialtykkelse rustfritt stål	1 mm
Maks. bearbeidbar materialtykkelse stålplate	1,65 mm
✂ hull	55,7 x 13,9 mm
Pakkeenhet	1 stk.
Nettovekt	0.89
Bruttovekt	0.903
Tolltariffnummer	82073010

Funksjoner

EAN	4028177808591
ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047