Rittal - The System.

Faster – better – everywhere.





KX 1301.000 E-Box KX

State: 11/12/2025 (Source: rittal.com/nz-en)



KX 1301.000 - E-Box KX Stainless steel

The stainless steel E-Box KX provides user-friendly assembly as well as flexibility when choosing your lock system. The 180° hinges supplied as standard provide excellent accessibility to the enclosure interior.







Features

Model No.	KX 1301.000
Product description	The stainless steel E-Box KX provides user-friendly assembly as well as flexibility when choosing your lock system. The 180° hinges supplied as standard provide excellent accessibility to the enclosure interior.
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4404 (AISI 316L)
Surface finish	Enclosure and cover: Brushed, grain 180 Mounting plate: Zinc-plated
Supply includes	Mounting plate Cam lock with 3 mm double-bit insert
Protection category to IEC 60 529	IP 66

© Rittal 2025

Features

Type rating to UL 50E	Type 1 Type 3R
	Type 3RX
	Type 4
	Type 4X
	Type 12
Dimensions	Width: 200 mm
	Height: 300 mm
	Depth: 155 mm
Dimensions mounting plate (W x H)	175 mm x 275 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Lock	Number of locks: 1
Basic material	Stainless steel 1.4404 (AISI 316L)
Packs of	1 pc(s).
Net weight	3.88
Gross weight	3.889
Customs tariff number	84879059
EAN	4028177919037
E-Number Sweden	E3465169
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

© Rittal 2025 3

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity

Tender text

Enclosure (E-Box, stainless steel)

Enclosure with door:

Stable stainless steel design, body folded from a single piece and welded, with protection channel all-round door opening, with PE conductor connection in the enclosure, solid rear panel with knockouts, door hinged on r/h side, with foamed-in PU seal, earthing in the door via bolt, with cam lock with 3 mm double-bit insert to DIN 43668, with mounting plate.

QR code:

QR code printed on body, cover and rating plate for clear identification and easy retrieval of relevant product information and documentation, and for clear traceability of the individual parts. Accessories: Top hat rail, wall mounting bracket, Mini-comfort handle.

Material:

Enclosure, door: Stainless steel 1.4404 (AISI 316L)

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

Brushed, grain size 180

Protection category to IEC 60 529: IP 66 Protection category to UL 508A: Type 4X Dimensions (W x H x D): 200x300x155 mm

Dimensions mounting plate (W x H): 175 x 285 mm

Model No.:1301.000

© Rittal 2025 4

Manufacturer: Rittal GmbH & Co. KG

© Rittal 2025 5