Rittal – The System.

Faster – better – everywhere.





KL 1523.010 Terminal boxes KL

State: 18/11/2025 (Source: rittal.com/nz-en)



KL 1523.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

Features

Model No.	KL 1523.010	
Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foame		
Surface finish	Enclosure and cover: Brushed, grain 180	
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes	
Protection category NEMA	NEMA 4X	
Protection category to IEC 60 529	IP 66	
IK Code	IK08	
Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm	
Material thickness - cover	1.25 mm	
Material thickness - enclosure	1.25 mm	
Lock	Number of locks: 4	
Basic material	Stainless steel 1.4301 (AISI 304)	
Packs of	1 pc(s).	
Net weight	1.7	
Gross weight	1.77	
Customs tariff number	84879090	
EAN	4028177008489	
E-Number Sweden	E3404365	
ETIM 9	EC000261	
ETIM 8	EC000261	

© Rittal 2025

Features

SS 8.0 27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

Tender text

Stainless steel terminal box without gland plate, protection cat. IP 66

Enclosure:

of 1.25 mm stainless steel 1.4301 (AISI 304), folded and welded from

a single piece, with all-round protection channel on the cover aperture. Cover of 1.25 mm stainless steel, sealed, with foamed-in special cover seal, facilities for connecting PE conductors in the cover and box, profile strips on both internal sides with mounting holes. Special plastic bush guards against accidental loss of the cover screws and provides screwdriver guidance.

Accessories:

quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate Surface finish:

brushed

Dimensions (W x H x D): 200 x 200 x 80 mm

© Rittal 2025 3