

# Rittal – The System.

Faster – better – everywhere.



## SG 2368.000

## Connection component

State: 6/04/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2368.000 - Connection component for signal pillar, modular

Optionally for conduit or wall/base mounting, with cover for optical components.

## Features

Model No.	SG 2368.000
Design	for conduit mounting
Product description	Optionally for conduit or wall/base mounting. Screw terminals in the connection component. With cover for optical components. Contact hazard protection to VDE.
Benefits	Simple assembly and contact via bayonet fastener.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide
Colour	Black
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Signal pillar	modular
Dimensions	Height: 43 mm
Protection category to IEC 60 529	IP 54
Rated operating voltage	12 V - 240 V (AC/DC)
Packs of	1 pc(s).
Net weight	0.11 kg
Gross weight	0.115 kg
Customs tariff number	85369095
ECLASS 8.0	27371232

# Features

---

Product description

SG Connection element, for signal pillar, modular, for conduit mounting

# Approvals

---

Approvals

UL + C-UL (listed)  
UR